



## Pressure Transmitter HDA 4300 shipping applications

Relative pressure

Accuracy 0.5 %



### Description:

This pressure transmitter has been specially developed for shipbuilding applications and is based on the HDA 4000 series.

The HDA 4300 has a ceramic measurement cell with thick-layer strain gauge for measuring relative pressure in the low pressure range.

The evaluation electronics converts the measured pressure into a proportional analogue signal of 4 .. 20 mA.

The electronic module is completely potted to protect it against humidity, vibrations and shock, and is enclosed in a solid stainless steel housing.

For use in the shipping industry, these pressure transmitters have been approved by the following organisations.

### Approvals:

- American Bureau of Shipping
- Lloyds Register of Ships
- Det Norske Veritas/  
Germanischer Lloyd
- Bureau Veritas



Other approvals on request

### Technical data:

#### Input data

Measuring ranges	bar	1	2.5	4	6	10	16	25	40	-1 .. 5	-1 .. 9
Overload pressures	bar	3	8	12	20	32	50	80	120	20	32
Burst pressure	bar	5	12	18	30	48	75	120	180	30	48

Mechanical connection G1/4 A ISO 1179-2

Tightening torque, recommended 20 Nm

Parts in contact with fluid Mech. connection: Stainless steel  
Sensor cell: Ceramic  
Seal: FKM/EPDM  
(as per model code)

#### Output data

Output signal, permitted load resistance	4 .. 20 mA, 2-conductor $R_{Lmax} = (U_B - 10 V) / 20 \text{ mA} [\text{k}\Omega]$
Accuracy acc. to DIN 16086, terminal based	$\leq \pm 0.5 \% \text{ FS typ.}$ $\leq \pm 1 \% \text{ FS max.}$
Accuracy, B.F.S.L.	$\leq \pm 0.25 \% \text{ FS typ.}$ $\leq \pm 0.5 \% \text{ FS max.}$
Temperature compensation Zero point	$\leq \pm 0.02 \% \text{ FS} / ^\circ\text{C typ.}$ $\leq \pm 0.03 \% \text{ FS} / ^\circ\text{C max.}$
Temperature compensation Span	$\leq \pm 0.02 \% \text{ FS} / ^\circ\text{C typ.}$ $\leq \pm 0.03 \% \text{ FS} / ^\circ\text{C max.}$
Non-linearity acc. to DIN 16086, terminal based	$\leq \pm 0.5 \% \text{ FS max.}$
Hysteresis	$\leq \pm 0.4 \% \text{ FS max.}$
Repeatability	$\leq \pm 0.1 \% \text{ FS}$
Rise time	$\leq 1 \text{ ms}$
Long-term drift	$\leq \pm 0.3 \% \text{ FS typ.} / \text{ year}$

#### Environmental conditions

Compensated temperature range	-25 .. +85 °C
Operating temperature range <sup>1)</sup>	-30 .. +85 °C / -25 .. +85 °C
Storage temperature range	-30 .. +100 °C
Fluid temperature range <sup>1)</sup>	-30 .. +100 °C / -25 .. +100 °C
CE mark	EN 61000-6-1 / 2 / 3 / 4

Vibration resistance acc. to DIN EN 60068-2-6 at 5 .. 500 Hz  $\leq 20 \text{ g}$

Protection class acc. to DIN EN 60529 <sup>2)</sup> IP 67

#### Other data

Supply voltage	10 .. 32 V DC
Residual ripple of supply voltage	$\leq 5 \%$
Life expectancy	> 10 million cycles, 0 .. 100 % FS
Weight	~ 150 g

Note: Reverse polarity protection of the supply voltage, excess voltage, override and short circuit protection are provided.



**FS (Full Scale)** = relative to complete measuring range

**B.F.S.L.** = Best Fit Straight Line

<sup>1)</sup> -25 °C with FKM or EPDM seal, -30 °C on request


<sup>2)</sup> With mounted mating connector in corresponding protection class

## Dimensions:




## Pin connections:

EN175301-803



Pin	HDA 4345-A
1	Signal +
2	Signal -
3	n.c.
L	Housing

M12x1



Pin	HDA 4346-A
1	Signal +
2	n.c.
3	Signal -
4	n.c.

## Model code:

**HDA 4 3 4 X - A - XXXX - S00 - X 1**

### Mechanical connection

4 = G1/4 A ISO 1179-2

### Electrical connection

5 = male, EN175301-803, 3 pole + PE  
(IP 67 mating connector supplied)

6 = male M12x1, 4 pole  
(mating connector not supplied)

### Output signal

A = 4 .. 20 mA, 2-conductor

### Measuring ranges in bar

01.0; 02.5; 04.0; 06.0; 0010; 0016; 0025; 0040  
0005 (-1 .. 5); 0009 (-1 .. 9)

### Modification number

S00 = with approvals for shipping

### Sealing material (in contact with fluid)

F = FKM seal (e.g. for hydraulic oils)

E = EPDM seal (e.g. for refrigerants)

### Connection material (in contact with fluid)

1 = stainless steel

### Accessories:

Appropriate accessories, such as mating connectors, can be found in the Accessories brochure.

## Note:

The information in this brochure relates to the operating conditions and applications described.

For applications or operating conditions not described, please contact the relevant technical department.

Subject to technical modifications.

### HYDAC ELECTRONIC GMBH

Hauptstraße 27, 66128 Saarbrücken

Germany

Telephone +49 (0)6897 509-01

Fax +49 (0)6897 509-1726

E-mail: [electronic@hydac.com](mailto:electronic@hydac.com)

Internet: [www.hydac.com](http://www.hydac.com)